


LabelManager™ 420P



High-Performance Portable Label Maker with PC or Mac® Connection

- Use standalone – or connect via USB to your PC or Mac®*
- Large 4-line backlit display
- Rechargeable battery pack
- Prints barcodes: UPC-E, Code 39, Code 128, EAN 13, EAN 8, UPC-A
- Print up to 10 copies of the same label
- Create labels with 7 font sizes, 8 font styles 10 text styles, and 8 boxes plus underline
- Store and quickly access up to 15 frequently-used labels
- Quick access buttons to punctuation / currency / other symbols / diacriticals

* Compatible with Windows Vista®, Windows® 7, Windows® 8, Mac OS® X 10.5 or later - Intel® only



Single Unit Includes:

- LabelManager 420P Label Maker
- D1 Starter Label Cassette, Black on White, 19mm x 3m
- Rechargeable Battery Pack
- Charging Adapter
- USB Cable
- Quick Start Guide
- 2-Year Limited Warranty Card



Quick Specs	
Unit Dimensions (H x W x L)	104 x 215 x 57 mm
Weight (excluding battery)	415 g
Mac®/PC Compatible	Yes
Accepts Label	6, 9, 12, 19mm
Tape Platform	D1, IND
Resolution	180 dpi
Printing System	Thermal Transfer
Print Speed	12mm/sec
Barcodes	Yes
Cutter Type	Manual
Batteries	Rechargeable
Adapter	Yes (included)
Networking	No
Country of Origin	China

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (kg)	QTY	EAN	Customer Price	
S0915490	LabelManager 420P ABC UK	Unit	10.0	18.7	25.0	1.0	1	3501170915493		
		Shelf	-	-	-	-	-	-	-	
		Case	39.0	26.5	32.0	6.5	6	13501170915490		
		Pallet	120.0	80.0	111.0	181.1	144			
Accessories										
1758459	Rechargeable Battery Pack	Unit	-	-	-	-	-	-		
S0895890	Charging Adapter	Unit	9.0	4.8	8.2	0.1	-	350 11708 95894		



D1 Standard*

For hundreds of tasks around the office or home office, such as filing, storage and asset tracking.

Temperature rating: -18°C to 90°C

*For use with LabelManager™ series and LabelWriter™ 450 Duo

D1 Compatible Labels														
Width	Length	A	A	A	A	A	A	A	A	A	A	A	A	
D1 STANDARD														
6mm	7mm	S0720780	S0720770	S0720790	-	-	-	-	-	-	-	-	43610	43610
9mm	7mm	S0720680	S0720670	S0720730	S0720710	S0720740	S0720720	-	-	S0720690	-	S0720700	-	
12mm	7mm	S0720530	S0720500	S0720580	S0720560	S0720590	S0720570	S0720600	S0720610	S0720540	S0720510	S0720550	S0720520	
19mm	7mm	S0720830	S0720820	S0720880	S0720860	S0720890	S0720870	S0720900	S0720910	S0720840	-	S0720850	-	



IND Vinyl

Ideal for both indoor and outdoor applications. Available in the widest range of colors that meet OSHA, ANSI and ISO color standards.

- UL recognized as a component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 80°C

IND Permanent Polyester

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

- UL recognized as a component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 150°C

IND Flexible Nylon

Specifically designed for curved surfaces and wire and cable marking.

- UL recognized as a component to UL 969
- RoHS compliant
- Temperature rating: -10°C to 80°C

For use with LabelManager™ series and LabelWriter™ 450 Duo and Rhino™ series

IND Compatible Labels													
Width	Length	A	A	A	A	A	A	A	A	A	A	A	A
IND VINYL													
9mm	5.5m	18443	-	-	-	-	-	-	1805437	-	-	-	-
12mm	5.5m	18444	-	18432	18435	1805413	1805416	1805435	1805414	1805243	1805415	1805412	
19mm	5.5m	18445	-	18433	18436	1805419	1805422	1805436	1805420	1805417	1805421	1805418	
24mm	5.5m	1805430	-	1805431	1805427	1805425	1805429	1805432	1805426	1805423	1805428	1805424	
IND PERMANENT POLYESTER													
6mm	5.5m	1805442	1805440	-	-	1805441	-	-	-	-	-	-	-
9mm	5.5m	18482	18508DM0	-	-	18485	-	-	-	-	-	-	-
12mm	5.5m	18483	622289	-	-	18486	-	-	-	-	-	-	-
19mm	5.5m	18484	622290	-	-	18487	-	-	-	-	-	-	-
24mm	5.5m	1734523	1805433	-	-	1805434	-	-	-	-	-	-	-
IND FLEXIBLE NYLON													
12mm	3.5m	18488	-	18490	-	-	-	-	-	-	-	-	-
19mm	3.5m	18489	-	18491	-	-	-	-	-	-	-	-	-
24mm	3.5m	1734524	-	1734525	-	-	-	-	-	-	-	-	-

Country of Origin: Belgium

DISTRIBUTED BY:
Newell Europe Sàrl
Chemin de Blandonnet 10
1214 Vernier – Switzerland
WWW.DYMO.COM

13-0103



A Newell Rubbermaid Brand

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.

©2014 Newell Europe LLC

A Newell Rubbermaid Company™

SCHAWK!

RMZ M Bina Business Park
Gurgaon - 122 001 India
No. 143, DCM, G, R, Road
Kandanchavallur Chennai 600 096 India
T: 91-44-4219 7777 | www.schawk.com



CYAN

MAGENTA

YELLOW

BLACK

Use the PANTONE MATCHING SYSTEM for accurate color reproduction

VERSION

5

DATE : 10-15-2014
OPERATOR : SR

NOTE:

JOB DESCRIPTION: NRM_EU_Writing_Dymo_1362812_EMEA Product Handbooks_UK Masters
FILE NAME : DY_1362812_2014_EMEA_LM420P_TechSheet_v5.indd

BRAND : WRITING-DYMO

SCHAWK JOB # : 310253V
NRM JOB # : 1362812
COMPONENT # : N/A

CATEGORY OF WORK : COLLATERALS-FACT BOOKS
NO. OF PAGES# : 2 PAGE
SIZE : A4