

TECHNICAL DATA SHEET

PRO-ELEC

**RoHS
Compliant**

Cable Gland M20 x 1.5 with Locknut Model: CB20620

Material	PA Nylon
Seal and washer	No washer supplied - IP68 when fitted with suitable washer
Properties	zero halogen, VDE approved

Size	Description	Thread	Cable size
16mm	Gland Nylon Grey with 15mm extra body	16mm	5-10mm
20mm	Gland Nylon Grey with 15mm extra body	20mm	6-12mm



Important Notice : This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELECs liability for death or personal injury resulting from its negligence.

PRO-ELEC