




SPECIFICATION CONTROL DRAWING Crystal Resonator

FREQUENCY

12.000000MHz



Holder Style	3X25X06 4-Pad
Mode	Fundamental
Adjustment Tolerance	± 30PPM at 25°C
Temperature Stability	± 50 PPM
Operating Temp. Range	-10°C to +60°C
Load Capacitance	18 pF
ESR	80 Max Ohm
Static Capacitance (C0)	Unspecified pF
Ageing	+/-5ppm 1st Year Max
Marking	AEL12.0 ww/yy

Amdt Date	Change Note	AEL Code
		X12M000000S719
		Issue Ref A