




**SPECIFICATION
CONTROL DRAWING
Crystal Resonator**

FREQUENCY

18.432000MHz



Holder Style	3X25X06 4-Pad
Mode	Fundamental
Adjustment Tolerance	± 100PPM at 25°C
Temperature Stability	± 100 PPM
Operating Temp. Range	-40°C to +85°C
Load Capacitance	16 pF
ESR	80 Max Ohm
Drive Level	0.1 Max mW
Static Capacitance (C0)	3.0 Max pF
Ageing	+/-2ppm 1st Year Max
Marking	AEL18.432 WWYY

Amdt Date	Change Note	AEL Code	
8 JAN 19	ESR Updated	X18M432000S049	
19 FEB 19	Package Updated	Issue Ref	B