






SPECIFICATION CONTROL DRAWING Crystal Resonator

FREQUENCY
24.000000MHz



**Recommended
Solder Pattern**



Holder Style
Mode
Adjustment Tolerance
Temperature Stability
Operating Temp. Range
Load Capacitance
ESR
Static Capacitance (C0)
Ageing
Marking

2x16x05 4-pad
Fundamental
± 15PPM at 25°C
± 20 PPM
-40°C to +85°C
8 pF
50 Max Ohm
Unspecified pF
+/-3ppm/Yr Max
AEL
WWYY

Amdt Date	Change Note	AEL Code		
6 DEC 11	ESR Updated	X24M000000S076		
16 JUN 16	Package Updated	<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th style="width: 70%; background-color: #cccccc;">Issue Ref</th> <td style="text-align: center;">C</td> </tr> </table>	Issue Ref	C
Issue Ref	C			