




SPECIFICATION CONTROL DRAWING Crystal Resonator

FREQUENCY
24.000000MHz



<p>Holder Style Mode Adjustment Tolerance Temperature Stability Operating Temp. Range Load Capacitance ESR Static Capacitance (C0) Ageing Marking</p>	<p>1,6 x 1,2mm 4P Fundamental ± 20PPM at 25°C ± 20 PPM -40°C to +85°C 8 pF 150 Max Ohm Unspecified pF +/-2ppm / Year Max 24.000 / WWYY</p>
---	--

Amdt Date	Change Note	AEL Code		
		X24M000000S111		
		<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th style="width: 70%;">Issue Ref</th> <td style="text-align: center;">A</td> </tr> </table>	Issue Ref	A
Issue Ref	A			