


SPECIFICATION CONTROL DRAWING

38.400000MHz

FREQUENCY

Crystal Resonator



Holder Style Mode Adjustment Tolerance Temperature Stability Operating Temp. Range Load Capacitance **ESR** Static Capacitance (C0) Ageing

Marking

3X25X06 4-Pad Fundamental ± 10PPM at 25°C ± 25 PPM -40°C to +85°C 10 pF 50 Max Ohm Unspecified pF +/-3ppm 1st Year Max AEL38.400 ww/yy

Amdt Date	Change Note	AEL Code	
		X38M400000S005	
		Issue Ref	А