

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0369210310](#)
Status: **Active**
Overview: [L1NK Connector System](#)
Description: L1NK 396-to-L1NK 396 Off-the-Shelf (OTS) Cable Assembly, 3.96mm Pitch, Single Row, 1000.00mm Length, 3 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|---------------------------------------|
| Product Family | Cable Assemblies |
| Series | 36921 |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | L1NK 396-to-L1NK 396 |
| Overmolded | No |
| Overview | L1NK Connector System |
| Product Name | L1NK 396 |
| Type | Discrete Wire Assembly |
| UPC | 193264110735 |

Physical

| | |
|--------------------------------|----------------------|
| Cable Length | 1000.00mm |
| Circuits (Loaded) | 3 |
| Color - Resin | Black |
| Gender | Female-Female |
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 51.448/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Pitch - Mating Interface | 3.96mm |
| Plating min - Mating | 5.080µm |
| Plating min - Termination | 5.080µm |
| Single Ended | No |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 3.12mm |
| Wire Size AWG | 18 |
| Wire/Cable Type | UL 1015 |


Electrical

| | |
|-------------------------------|---------|
| Current - Maximum per Contact | 13.0A |
| Voltage - Maximum | 600V DC |

Material Info

Reference - Drawing Numbers

| | |
|---------------|---------------|
| Sales Drawing | 369210300-000 |
|---------------|---------------|



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[36921](#) Series

Mates With

L1NK 396 Headers [207478](#) , [207479](#)