

---

## SAC 4 Way Masthead Splitter 47-790MHz

---

**Product code: AE5024**

**Specifications:**

- Low insertion loss wideband masthead/outdoor splitter
  - LTE/4G Protected
  - All ports DC power pass
- Fully shielded with F type connectors
  - Low insertion loss
  - Masthead and wall mountable
- Number of inputs: 1 Number of outputs: 4
  - Input frequency band: UHF/VHF
  - Output frequency range: 47-790MHz
  - DC Pass: All ports 400mA Max - 75ohms
- Insertion loss: 47-750MHz: 7dB - 750-790MHz: 9.5dB
- Return loss: 47-750MHz: 10dB - Return loss: 750-790MHz: 12dB
- Isolation: 47-750MHz: 20dB - Isolation: 750-790MHz: 20dB
  - Out of band rejection: 790-820MHz: 45dB
  - Insertion loss: 930-960MHz: 55dB
- Contents: 1 x Splitter, 1 x Reusable tie-wrap
- Dimensions: 115x100x65 mm Weight: 0.236kg

