

---

## SAC 4 Way Masthead Amp + PSU Kit 10-25dB

---

Product code: AE5034

Specifications:

Dimensions: 160x134x60mm - Weight: 1.2 KG

- SAC 1 input 4 output variable wideband 470 ~ 790MHz masthead amplifier. 10-25dB variable gain. All ports DC powered. kit includes PSU.
  - All ports DC powered - Fully shielded with F type connectors
    - LTE/4G Protected - Tight seal waterproof housing
  - SMD circuit technology design - High output capability with low noise
    - Easy to install and convenient to use
      - Number of inputs: 1 - Number of outputs: 4
      - Input frequency band: UHF - Input channels: 21-60
    - Frequency range: 470-790MHz - Gain(variable): 10-25dB
      - Noise Figure: 3.8Db - DC output: 12V 100Ma
      - Power rating: 220~240V/50Hz - Insertion loss: 1dB
  - Operative temperature: -10°C ~ +40°C - Short-circuit protection: yes
    - Contents: 1 x Amp, 1 x PSU, 1 x reusable tie-wrap, 2 x screws

