

---

## SAC 5 Way Masthead Amp + PSU Kit 10-25dB

---

**Product code: AE5035**

**Specifications:**

- SAC 1 input 5 output variable wideband 470 ~ 790MHz masthead amplifier. 10-25dB variable gain. All ports DC powered. kit includes PSU.
  - Dimensions: 140x150x110mm - Weight: 1.3 KG
- All ports DC powered - Fully shielded with F type connectors
  - LTE/4G Protected - Tight seal waterproof housing
- SMD circuit technology design - High output capability with low noise
  - Easy to install and convenient to use - Number of inputs: 1
  - Number of outputs: 5 - Input frequency band: UHF
  - Input channels: 21-60 - Frequency range: 470-790MHz
    - Gain(variable): 10-25dB - Noise Figure: 4dB
    - Max output: 102dBuV - DC output: 12V 100mA
    - Power rating: 220~240V/50Hz - Insertion loss: 1dB
- Operative temperature: -10°C ~ +40°C - Short-circuit protection: yes
  - Contents: 1 x Amp, 1 x PSU, 1 x reusable tie-wrap, 2 x screws
    - Dimensions: 150x140x110mm
    - Weight: 0.767kg

