




Kasa Spot

Indoor Security Camera



KC100



Features



Crystal Clear Video

1080p HD, 130° wide-angle video and night vision, make sure you never miss a thing day or night.



Night Vision

Even at night, the camera will detect activity 20 ft. away with Night Vision.



Four Customizable Activity Zones

Create multiple dynamic activity zones around areas that are important and receive alerts you care about.

Live View

keep an eye on what's important to you real-time from anywhere with the Kasa Smart app.

Cloud Services

Add Cloud Services for video recording and other intelligent features with a Kasa Care subscription plan*.

*Upgrade to a Kasa Care subscription plan and enjoy full video recordings up to 30 days. Visit [Kasasmart.com](https://kasasmart.com) for details.

Two-Way Talk

Communicate with others with the built-in microphone and speaker.

Specifications

Camera

Image Sensor: 1/2.7"(Φ6.6)
Resolution: 1080p HD 15 fps
Night Vision: 850 nm IR LED up to 20 ft
Lens: F/NO: 2.0; Focal Length: 3.21mm
Viewing Angle: FOV = 130°

Audio

Audio Communication: 2-way audio
Audio Input & Output:
Built-in microphone and speaker

Video

Video Compression: H.264
Frame Rate: 15fps
Video Streaming: 1080p
Audio Compression: AAC

Activity Notifications

Input Trigger:
Motion detection, Audio detection
Output Notification:
Push notification

Hardware

Button: RESET button
Indicator LED: System LED
Adapter Input: 100-240VAC, 50/60Hz, 0.2A
Adapter Output: 5.0VDC, 1.0A
Dimensions (W x D x H):
2.3 x 2.0 x 3.5 in. (59 x 49.6 x 88.6 mm)

Network

Wireless Rate:
11Mbps(802.11b)
54Mbps(802.11g)
150Mbps(802.11n)
Frequency:2.4GHz
Wireless Security: WEP, WPA/WPA2-PSK
Security: 128 bit AES encryption with SSL/TLS

System

Regulatory Certification:
FCC, IC, CE
System Requirements:
iOS 9+, Android 4.4x+

Environment

Operating Temperature:
0°C~40°C (32°F~104°F)
Storage Temperature:
-20°C~70°C (-4°F~158°F)
Operating Humidity:
10%~90%RH non-condensing
Storage Humidity:
5%~90%RH non-condensing

Package Contents

Kasa Spot
Power Adapter
10 ft USB Cable
Quick Start Guide
Mounting Screws
Mounting Template

