



Specification:

Material:

1. Plastic Housing :ABS
2. RJ45 contact material & finished:
 - 3-1.Phosphor Bronze with Nickel plated.
 - 3-2.Contact area : Gold plated.

Performance:

- a. The sticker color codes combine two wirings of T568A & T568B.
- b. Insertion Force: 900 gms for 8 contacts.
- c. Retention Strength: 7.7 kgs between Jack and Plug.
- d. Operation Temperature: -20° to 68°.
- e. Durability:
 - Jack : 750 cycles Plug-Jack mating and unmating test,
- f. The Cat.6 performance is in compliance with the ANSI/TIA/EIA 568 C standard.

			Tolerance: X. ±0.5 .X ±0.3 .XX ±0.10	SCALE: FREE	CUSTOMER:	PRO-SIGNAL		Approved by
			Angle: X° ±3° .X° ±1°	UNIT: mm		CUSTOMER P/N:	COMPANY P/N: CS32795	Checked by
REV.	DESCRIPTION	DATE	REV. : OO	SHEET		2:1	DWG. No. :	TITLE: UTP CAT6 COUPLER