



# 5x20mm low profile panel mounting fuseholders

## Product overview


- Low profile panel mounting
- Moulded in UL94-V0 PBT
- Screw driver release
- Screw and bayonet carrier
- 2.8 and 4.8 quick connect terminals
- Anti-rotation D fixing
- EN60127-6
-    approved

PART NO.	CARRIER	TERMINAL	SPECIFICATION	
CFH04	Screw	Solder / 2.8mm quick connect	Rating	10A / 250V
CFH09	Bayonet	Solder / 2.8mm quick connect	Contacts/resistance	Tinned nickel plated brass, <math><5m\Omega</math>
CFH12	Bayonet	Solder / 4.8mm quick connect	Moulding	UL94-V0 flame retardant PBT
			Dielectric strength	3kV / 60"
			Power dissipation	2.5W (VDE)
			Insulation resistance	>100M $\Omega$
			Operating temperature	-30°C to +85°C
			Shocksafe category	PC2


CFH04



CFH09



CFH12



## KEY FEATURES

Quick connect tabs | Anti rotation body moulding | Screw or bayonet release options