


PCB TERMINAL BLOCKS

7.5mm Pitch Commercial Low Profile Screw Terminal Blocks

- 2 & 3 pole solid block
- End stackable
- Moulded in green UL94-V0 flame retardant PA66
- Wire protector terminals
- 0.5-4.0mm² (30-12AWG) solid cable
- 0.5-2.5mm² (30-12AWG) stranded cable
- Captive screws
- Anti solder wicking terminal
- Guided pin alignment
-  approved


CTB55VK



TYPE NO.	POLES	LENGTH
CTB55VK/2	2	15mm
CTB55VK/3	3	22.5mm

SPECIFICATION

Rating	24A/500V
	UL=16A/300V, VDE&IMQ=24A/750V
Dielectric strength	3kV
Impulse withstand voltage	6kV
Working temperature	110°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Tinned, nickel plated brass
Wire Protector	Tin plated, phosphor bronze
Screw/torque	M2.5 steel zinc plated, 0.4Nm
Recommended PCB hole size	ø1.3mm



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

DIN RAIL
ENCLOSURES

BATTERIES

SOLAR
PANELS

TRANS-
FORMERS



+44 (0)1638 716101
info@camdenboss.com
www.camdenboss.com

We operate a constant improvement policy, our products are subject to change without notice.

Ver 1.1

