


500 series small flanged ABS boxes

Product overview

A comprehensive range of ABS boxes with flush-fitting lid and flanged body for partial or complete potting of electronic components.

- Moulded in ABS UL94-HB
- Flush-fitting lid mounted by 4x fixing screws
- Lugs provide added security once mounted by restricting access
- Flanged body with 4x mounting holes
- Ideal for partial or complete potting
- Compliant with water absorption specifications to DIN53495
- High-rigidity and impact strength
- Highly resistant to most chemicals



SPECIFICATION

Materials	Lid and base ABS, UL94-HB
Operating temperature	-20°C to +80°C
Standard colours	Black
Standard unit includes	Lid and base 4x screws

*UL94-V0 to order

BLACK	LENGTH	WIDTH	HEIGHT
RX505A	36mm	26mm	17mm
RX506A	42mm	30mm	19mm
RX507A	48mm	34mm	21mm
RX508A	56mm	40mm	24mm
RX509A	66mm	46mm	26mm
RX510A	76mm	52mm	29mm

KEY FEATURES

Moulded in ABS, UL94-HB | Flanged body | Flush-fitting lid

