

VR IP CAMERA 360°

Enjoy every time with the family

ENER-J®
Smart Home Living



PANORAMIC VR IP CAMERA 360°

SKU Code: IPC1014
EAN Code: 7103351794123

HD 360° Panoramic Fisheye IP Camera Wifi Security Surveillance Monitor VR 3D Cam

960P Wifi IP Camera
360° Panoramic



YooSee
Android iOS

Features

- The VR CAM camera is a panoramic equipment designed to provide optimal surveillance coverage for both homes and businesses.
- The IP cameras are connected to the local network via cable or wireless over Wi-Fi. Access is done over the network by any computer, allowing you to view and record the images with perfect quality thanks to the digital video system. To monitor remotely, just have an internet connection at the installation site and a configured router.
- Equipped with a 360° overview, the camera is perfect for monitoring large spaces such as sales floors, warehouses, offices, small shops, buses, and other vulnerable areas such as showrooms, living rooms, master bedrooms, and a lot more.

Specifications	
Model	IPC1014
Chipset	GM8135+1135
Video Compression	H.264 High profile @Level 4.1/Motion JPEG
Main Processor	High Performance DSP
Image Sensor	1/3" CMOS
Effective Pixels	1.3 Mega Pixels
Maximum Resolution	1280*960
Video Bit Rate	32kbps-6mbps adjustable
Video Stream	Multiple H.264, M-JPEG Video stream, at maximum resolution to 25 FPS while the sync output of multi-channel video stream
Audio	Support, audio format : G711/726
Camera Module	
Lens	Standard 1.44mm
Min. illumination (LUX)	Color: 1.0/F1.2; Monochrome: 0.01/F1.2; IR: 0
Feature	Visual angle: 360° wide visual angle
Network	WiFi
Network Protocols	IPv4, TCP/IP, UDP, HTTP, RTP/RTCP/RTSP, FTP, UPnP, DDNS, NTP, IGMP, ICMP
Access Protocol	Standard ONVIF2.0 protocol, GB28181 protocol
Safety	Password protection, multi-user access, access authorized
System integration	
APP interface	Support integrated API, SDK
Connection mode	Support wireless AP mode, wifi connect and wired connect
IR distance	3 pieces infrared lights, IR distance up to 20-30M
Connect mode	Wireless hot spot AP mode, wifi connect and wired connect
Local storage	Support micro-SD card, max 64GB
Wi-Fi	Support wifi connection
P2P	Support P2P remote monitoring, no cabling, plug and play
Voice intercom	Support voice intercom between the APP and the camera (Two ways Audio)
Power supply	DC12V 2A
Power consumption	<10W
Working environment	Working temperature -20°C~+55°C; working humidity ≤ 95%
Housing	Engineering plastic materials
IP rating	IP52
Dimension (mm)	No package: 154*165, Package: 290*150*170
Weight (kg)	No package : 0.5, Package : 0.79
Installation	Ceiling installation