

Product Code: EH1712



Prem-I-Air 45W Tubular Heater

Prem-I-Air tubular heaters are designed to be a low cost solution when steady background heat is required. Being IP55 rated they are ideal for use as frost protection heaters or for general background heating and are suitable for use in cloakrooms, conservatories, greenhouses, airing cupboards, portable buildings etc. and can help to remove dampness and condensation. Made from tubular metal the unit is supplied with metal fixing brackets. Safety protection cages are available as a separate line.



Features:

- Ideal for Low Level Back Ground Heating
- IP55 rating
- Supplied with Mounting Brackets
- Easy to Use

PRODUCT SPECIFICATIONS

Depth (mm).....	55
Display Footprint (mm)	305x75x55
Gross Weight (Packaged) (kg)	0.86
Gross weight outer carton (kg).....	5.16
Item priced per	1
Net weight (kg)	0.7
Outer box (HxWxD mm)	405x275x190
Outer box quantity	6
Packaging.....	Picture box
Paper weight (kg).....	0.1
Plastic weight (kg).....	0.06
Product Dimensions (mm).....	305x75x55
Product EAN	5021196757269

Width (mm)	75
Colour.....	White
Frequency (Hz)	50
Overheat safety cut out	yes
Plug Amp (A)	3
Protection class I or II.....	I
Height (mm)	305
Packaged dimensions (HxWxD mm).....	390x87x87
Transport dimensions (mm).....	390x87x87
Voltage	230
Power (W).....	45