

Product Code: EH1718



Prem-I-Air 180W Tubular Heater

Prem-I-Air tubular heaters are designed to be a low cost solution when steady background heat is required. Being IP55 rated they are ideal for use as frost protection heaters or for general background heating and are suitable for use in cloakrooms, conservatories, greenhouses, airing cupboards, portable buildings etc. and can help to remove dampness and condensation. Made from tubular metal the unit is supplied with metal fixing brackets. Safety protection cages are available as a separate line.



Features:

- Ideal for Low Level Back Ground Heating
- IP55 rating
- Supplied with Mounting Brackets
- Easy to Use

PRODUCT SPECIFICATIONS

Depth (mm).....	55
Display Footprint (mm)	1220x75x55
Gross Weight (Packaged) (kg)	2.67
Gross weight outer carton (kg)	16.02
Height (mm).....	1220
Item priced per	1
Net weight (kg).....	2.06
Outer box (HxWxD mm).....	1370x275x190
Outer box quantity	6
Packaged dimensions (HxWxD mm)	1350x87x87
Packaging.....	Picture Box
Paper weight (kg).....	0.5
Plastic weight (kg)	0.11
Product EAN	5021196757320

Transport dimensions (mm)	1350x87x87
Width (mm)	75
Colour	White
Frequency (Hz)	50
Plug Amp (A)	3
Power (kW)	0.180
Protection class I or II.....	I
Voltage	230
Product Dimensions (mm)	1220x55x75
Power (W).....	180
Overheat safety cut out	yes