

DURATOOL

3.5 inch IP Camera Tester

Applications:

- Analog camera test
- IP camera test, support 4K, H.264 and H.265

Features:

- 3.5 inch wide angle touch screen, 480*320 resolution
- H.264 and H.265, 4K video display via mainstream
- PPPOE Dial test, can connect internet to PPPOE dial test
- IP & CVBS camera test, PTZ controller
- Rapid video, just by one key to detect all network cameras and auto display
- Onvif, auto log in and display image from the camera, activate Hikvision camera, and also can create testing report
- Screen management, change function's icons order
- Built in Wi-Fi, display image from the wireless camera, create wifi hotspot
- 4K video files and MKV/MP4 media files play
- DC 12V / 1A power output
- IP discovery, it can auto-scan the whole network segment IP, and auto-modify tester's IP address
- Display its genuine resolution of the IP camera images
- PTZ control supports more than 30 protocols such as PELCO-P, PELCO-D, and SAMSUNG
- Ping test, ip address scan, port flashing etc.
- Audio in, support record and save the audio, calculators, music players and other application tools
- 3.7 V /3000mAh Lithium Ion Polymer Battery, after 3~4 hours charging, working time lasts 8 hours
- Compatible with 8MP TVI, 8MP CVI, 8 MP AHD cameras



Specification

Model Number	D03352
Display	3.5 inch wide angle touch screen, 480*320 resolution
CVBS	1 channel BNC input & 1 channel BNC looped output, NTSC/PAL (Auto adapt) PTZ control, RS485 control, Baud 600-115200bps, compatible with more than 30 protocols such as PELCO-D/P, Samsung, Panasonic etc.
IP camera test, 4k / H.265 / H.264	IP Discovery / Quick Onvif / IPC test / RTSP play / Client APK Rapid Video, auto view the video, create testing report Hik test tool, pressing just one key to activate hikvision camera, Image test, can modify the user name, password and IP parameters Dahua test tool, Dahua camera test, modify the user name, password and IP parameters
Zoom Image	4x zoom, to enlarge image, Screen snapshot, record ,save ,view and record and play back
Network Port	10/100/1000M auto adapt, RJ45
Power output	DC12V 1A power output, supply temporarily power for the camera

Network test	Trace route, Link monitor, DHCP server, port flashing, Ping test
Wi-Fi	Built in WIFI, speeds 150M, display wireless camera image
Audio test	1 channel audio signal input
Data monitor	Captures and analyzes the command data from controlling device, also can send hexadecimal
External power supply	DC 5V 2A
Battery	Built-in 3.7V Lithium polymer battery, 3000mAh
Rechargeable	After charging 3-4 hours, normal working time 8 hours
Operation setting	OSD menu, select your desired language: English, Korean, Russian, Italian, French, Polish, Spanish, etc
Auto off	1-30 (mins)
Working Temperature	-10°C---+50°C
Working Humidity	30%-90%
Dimension	120mm x 80mm x 30mm (Tester); 200mm x160mm x 70mm (box)
Weight	300g (Tester); 800g (Tester with spare parts, box)