


HD-TVI Dual Voltage Indoor Dome Camera with Built-In IR LEDs

HLED33DTB 2.8-12mm auto iris varifocal lens, black housing
HLED33DTW 2.8-12mm auto iris varifocal lens, white housing

Features

- Full HD resolution over coax @ 30FPS
- IR Range: 65'
- Smart DNR reduces noise in low light
- Smart IR reduces saturation of objects within close proximity to IR LEDs
- 3-axis design, both wall and ceiling mountable
- Digital wide dynamic range
- OSD for camera setting adjustments
- 12VDC/24VAC dual voltage operation
- 5 year warranty
- Additional analog output for 960 H

HD TVI **IR**



Specifications

Image Sensor 1/3" progressive scan CMOS 2 MP
Resolution..... 1920 x 1080
Minimum Illumination..... 0 lux with IR on
S/N Ratio 50dB
Effective Pixels 1984 (H) x 1105 (V)
Total Pixels 2000 (H) x 1121 (V)
Shutter 1/30 sec – 1/300,000 sec
Number of IR LEDs 24
IR Range 65 ft. (depending on scene reflection)
OSD..... Yes
Synchronization Internal
Privacy..... On / Off (8 zones)
Motion Detection..... On / Off (4 zones)
Mirror On / Off

DNR..... High / Middle / Low / Off
White Balance ATW / Push / Manual
Image..... BLC / HLC / D-WDR / Defog
AGC..... Level adjustable (0-20)
TV System..... NTSC
Housing High impact ABS
Operating Temperature.. 14° F - 122° F
Power Supply 12VDC, 24VAC (power supply not included)
Power Consumption 350mA
Dimensions..... 4.4" (Dia.) x 3.4" (H)
Weight 8 oz.
Included in Package Main unit, mounting screws, test monitor lead, DC lead, user manual

Optional Accessories



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply



TVIUTPPT
HD Video
Transceiver with
Pigtail (Balun)



TVIUTP
HD Video
Transceiver