

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1731120138](#)  
**Status:** **Active**  
**Overview:** [FCT D-Sub Connectors](#)  
**Description:** FCT Pneumatic Contact, Female, Straight, 2.00mm Tube Inner Diameter

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	D-Sub Products
Series	<a href="#">173112</a>
Brochure Order No	987651-9941
Contact Type	Pneumatic
Exclude SD Check	Yes
Overview	<a href="#">FCT D-Sub Connectors</a>
Product Category	Contacts
Product Name	FCT Products
Type	Mixed Layout
UPC	889056488938

**Physical**

Durability (mating cycles max)	500
Gender	Female
Material - Contact	Metal Alloy
Material - Retaining Clip	PEI
Net Weight	1.200/g
Orientation	Straight
Packaging Type	Bag
Plating - Contact	N/A
Temperature Range - Operating	-10° to +60°C

**Electrical**

Current - Maximum per Contact	N/A
-------------------------------	-----

**Material Info**

Engineering Number	FMG002S149KR
--------------------	--------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[173112 Series](#)

**Use With**

FCT Mixed Layout Connectors