






		Conditions
cell type:	NiMH	
cell size:	AAA	
nominal voltage:	1.2 V	
max. charge voltage:	1.5 V	at standard charge (0.1C / 20°C)
capacity		
nominal:	800 mAh	discharge at 0.2C
minimum:	800 mAh	discharge at 0.2C
	750 mAh	discharge at 1C
		1.0V end discharge voltage
		ta: 20°C
max. continuous discharge current:	2400 mA	ta: 0...45°C
charge		
standard charge:	current 80 mA	time 14....16hrs
quick charge:	240 mA	4hrs
fast charge:	800 mA	1.1hrs
recommended charge termination control parameters:	0...5 mV 0.8...1 °C 45...50 °C	-ΔV (-delta V) temperature rise per minute TCO (temperature cut off)
trickle charge current:	8...25 mA	(recommended)
continuous overcharge: (less than 1 year)	≤ 80 mA	no conspicuous deformation no leakage
internal resistance: (impedance)	≤ 60 mΩ	at 1KHz battery fully charged
life expectance:	≥ 500 cycles	acc. IEC standard
self discharge		
charge retention:	≥ 80 %	after 12 months storage at 20°C
initial capacity:	≥ 550 mAh	within 30 days after delivery discharge at 0.2C
ambient temperature range:	0...45 °C 10...40 °C - 20...65 °C - 20...50 °C - 20...40 °C - 20...30 °C	standard charge fast charge discharge storage (≤3months) storage (≤6months) storage (≤24months)

QCT1: 20/750/60
QCT2: 30/700/60

mechanical specifications		
cell dimensions		
diameter d1:		10.3 - 0.7 mm
diameter d2:	max.	3.8 mm
height h1:		44.5 - 1.5 mm
height h2:	min.	0.8 mm
weight:		12.5 ± 2 g



Diagrams



	ANSMANN Specifications for model:	NiMH Battery
		AAA - 800mAh low self discharge
	data sheet no. / part no.	
	supplier no.	702069
author / date	TG / 13.07.2018	

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice