



6W

VT-606RD 6W LED PREMIUM PANEL WITH SAMSUNG CHIP
 COLORCODE:3000K ROUND

Lumens 420	Beam Angle 120	Dimensions ?120x12mm
----------------------	--------------------------	--------------------------------

Warm White
 SKU:706



Technical Information

Output Voltage:	DC:12-24V	LED Chip Type:	SMD
Watts:	6	IP Rating:	IP20
Lumens:	420	Dimmable:	No
Shape:	Round	Warranty (Years):	5
Beam Angle:	120	PF:	>0.5
Cutting Size:	?110mm	CRI:	>80
Unit Color:	White	Operation Temperature:	-20°C to 45°C
Body Type:	Aluminium	Input Power:	AC:85-265V,50/60Hz
Long life:	30,000 Hours	Sensor Compatibility:	Yes

Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.205
Unit CBM	0.000756

Listing Details

EAN Code	3800157641623
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	40
Qty Per Pallet	1600

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES