



**18W**

VT-618SQ 18W LED PREMIUM PANEL WITH SAMSUNG CHIP  
COLORCODE:6400K SQUARE

Lumens <b>1500</b>	Beam Angle <b>120</b>	Dimensions <b>225x225x12mm</b>
-----------------------	--------------------------	-----------------------------------

White  
SKU:717



## Technical Information

Instant Start:	0-100% lt1Sec	LED Chip Type:	SMD
Output Voltage:	DC:36-72V	IP Rating:	IP20
Watts:	18	Dimmable:	No
Lumens:	1500	Warranty (Years):	5
Shape:	Square	PF:	>0.6
Beam Angle:	120	CRI:	>80
Cutting Size:	210x210mm	Operation Temperature:	-20°C to 45°C
Unit Color:	White	Input Power:	AC:85-265V,50/60Hz
Body Type:	Aluminium	Sensor Compatibility:	Yes
Long life:	20,000 Hours		

## Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.58
Unit CBM	0.00253

### Listing Details

EAN Code	3800157641739
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	480

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES