



275
LUMEN



1½-4H
RUNTIME



21M
RANGE



IP20/IK07
IP RATING

NEW IL-275R - RECHARGEABLE POCKET INSPECTION LIGHT

- High power 275 lumen cool white COB LED
- Additional 150 lumen cool white SMD LED top torch
- Super tough construction - IK07 shock resistant
- Durable rubber hand grip
- Rear stainless steel pocket clip attachment
- 360-degree swivel ball joint base
- Super strong magnetic base
- Easy press rear switch
- USB rechargeable - 1m micro-USB cable included

BATTERY 3.7v 700mAh Li-polymer Rechargeable Battery

WEIGHT 76g

DIMENSION 172 x 26.5 x 25 mm



TOP 150 LM FLASHLIGHT



MAGNETIC BALL JOINT BASE