



**22W**

VT-2207 22W LED SLIM PANEL LIGHT COLORCODE:4000K ROUND

Lumens <b>1800</b>	Beam Angle <b>120</b>	Dimensions <b>Ø240 x 12mm</b>
-----------------------	--------------------------	----------------------------------

Day White  
SKU:6423

**2 YEARS**  
WARRANTY

**SENSOR**  
COMPATIBLE



## Technical Information

Instant Start:	0-100% in 11s	IP Rating:	IP20
Watts:	22	Dimmable:	No
Lumens:	1800	Warranty (Years):	2
Shape:	Round	PF:	>0.9
Beam Angle:	120	CRI:	>80
Unit Color:	White	Operation Temperature:	-25 to +50°C
Body Type:	Aluminium	Input Power:	AC 85-265V, 50/60 Hz
Long life:	20,000 Hours	Sensor Compatibility:	Yes
LED Chip Type:	SMD		

## Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.667
Length(Box)mm	260
Width(Box)mm	320
Height(Box)mm	30
Unit CBM	0.002496

### Listing Details

EAN Code	3800157626958
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	480

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES