



22W

VT-2207 22W LED SLIM PANEL LIGHT COLORCODE:6400K ROUND

Lumens 1800	Beam Angle 120	Dimensions Ø240 x 12mm
-----------------------	--------------------------	----------------------------------

White
 SKU:6424

2 YEARS
 WARRANTY

SENSOR
 COMPATIBLE



Technical Information

Instant Start:	0-100% in 11s	IP Rating:	IP20
Watts:	22	Dimmable:	No
Lumens:	1800	Warranty (Years):	2
Shape:	Round	PF:	>0.9
Beam Angle:	120	CRI:	>80
Unit Color:	White	Operation Temperature:	-25 to +50°C
Body Type:	Aluminium	Input Power:	AC 85-265V, 50/60 Hz
Long life:	20,000 Hours	Sensor Compatibility:	Yes
LED Chip Type:	SMD		

Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.667
Length(Box)mm	260
Width(Box)mm	320
Height(Box)mm	30
Unit CBM	0.002496

Listing Details

EAN Code	3800157626965
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	480

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES