



40W

VT-5140 40W WIFI LED PANEL LIGHT-COMPATIBLE WITH AMAZON ALEXA AND GOOGLE HOME CCT:3 IN 1 DIMMABLE

Lumens 4800	Beam Angle 120	Dimensions 595x595mm
-----------------------	--------------------------	--------------------------------

3 IN 1
SKU:8080

2 YEARS
WARRANTY



Technical Information

Output Voltage:	DC:30-42V	Long life:	20,000 Hours
Watts:	40	LED Chip Type:	SMD
Lumens:	4800	IP Rating:	IP20
Shape:	Square	Dimmable:	Yes
On/Off Cycles:	>15000	Warranty (Years):	2
Beam Angle:	120	Operation Temperature:	-20°C to +45°C
Output Current:	950mA	Input Power:	AC:220-240V,50Hz
Unit Color:	White	Wireless Frequency:	2.4Ghz
Body Type:	Aluminium		

Features

- ✓ V-TAC's wifi enabled Smart Panel
- ✓ Functions with V-TAC Smart Light App
- ✓ Compatible with Alexa and Google Home
- ✓ Wireless frequency of 2.4 GHz
- ✓ Easy to Install and Pair to the app
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	3.6
Unit CBM	0.030057

Listing Details

EAN Code	3800157646215
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	5
---------------------------------	---

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES