

## Printer - BLUEMARK ID - 1003334

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Monochrome printer with UV LED technology, with integrated "MARKING SYSTEM APP" marking software on board. 7" touch color display for printing plastic tags in UC, UCT, US, and UM format, as well as metal plates.

### Your advantages

- ✓ The printer detects the direction of the inserted sheets and automatically rotates printing 180° if required
- ✓ Intuitive and time-saving operation using integrated marking software and a graphical user interface
- ✓ Marking that is instantly wipe-resistant, so that marking materials are ready for immediate use
- ✓ Rapid marking of plastic and metal plates for marking terminals, conductors, cables, devices, and plant marking
- ✓ Scalable print resolution between standard (300 dpi) and HD printing (600 dpi)
- ✓ Environmentally-sound, emission-free high-speed printer with modern UV LED technology



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 471075
GTIN	4055626471075
Weight per Piece (excluding packing)	30,500.000 g
Custom tariff number	84433210
Country of origin	Germany

### Technical data

#### General

Interface	10/100 Mbps Ethernet 1x USB 2.0 Device, 1x USB 2.0 Host
Weight	21 kg

#### Dimensions

Length	675 mm
Height	340 mm
Width	523 mm

# Printer - BLUEMARK ID - 1003334

## Technical data

### Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC
Additional text	50 Hz ... 60 Hz

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 6.0	19140100
eCl@ss 7.0	19140190
eCl@ss 9.0	19140190

### ETIM

ETIM 6.0	EC001672
ETIM 7.0	EC001672

## Approvals

### Approvals

#### Approvals

CSA / IECCEB Scheme / CSAus / EAC / cCSAus

#### Ex Approvals

### Approval details

CSA		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	70178753
-----	--	---	----------

IECEE CB Scheme		<a href="http://www.iecee.org/">http://www.iecee.org/</a>	NO102150
-----------------	--	---	----------

# Printer - BLUEMARK ID - 1003334

## Approvals

CSAus		<a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a>	70178753
-------	--	---	----------

EAC			RU *- DE.A*30.B.02513
-----	--	--	--------------------------

cCSAus			
--------	--	--	--

## Accessories

### Accessories

#### Magazine

Magazine - BM ID-ADAPTER PLATE-US - 1044355



Adapter plate for accommodating US sheets

Magazine - BM ID-MAG20 - 1044356



Infeed magazine for accommodating a max. of 20 UniCard sheets

Magazine - BM ID-MAG40 - 1044357



Infeed magazine for accommodating a maxi. of 40 UniCard sheets

## Printer - BLUEMARK ID - 1003334

### Accessories

Magazine - BLUEMARK MAG EM-M (27X15) - 0802736



Magazine, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG EM-M (27X18) - 0802737



Magazine, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG EM-M (49X15) - 0802738



Magazine, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG EM-M (60X15) - 0802739



Magazine, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG EM-M (60X30) - 0802740



Magazine, width: 76 mm, color: white

---

## Printer - BLUEMARK ID - 1003334

### Accessories

Magazine - BLUEMARK MAG EM-M (85,6X54) - 0802741



Magazine, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG EM-M (100X60) - 0802742



Magazine, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG WM-M (29X8) - 0802743



Magazine, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG WM-M (40X15) - 0802744



Magazine, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG WM-M (60X15) - 0802746



Magazine, width: 76 mm, color: white

---

## Printer - BLUEMARK ID - 1003334

### Accessories

Magazine - BLUEMARK MAG WM-M (D30) - 0802747



Magazine, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG AI-WM - 5146567



Magazine for BLUEMARK printer, for accommodating 0.5 - 1.5 mm<sup>2</sup> ferrules with insulating collar that can be labeled

---

Magazine - BLUEMARK MAG AI-WM 2,5 - 5146640



Magazine for BLUEMARK printer, for accommodating 2.5 mm<sup>2</sup> ferrules with insulating collar that can be labeled

---

Magazine - BLUEMARK MAG ZB - 5146529

Magazine for BLUEMARK, only for ZB 7,62 UV-100 - 0829029

---


Magazine - BLUEMARK MAG ZB 8/27 - 5146558



Magazine for BLUEMARK, only for ZB 8/27 UV-100 - 0829102

---

Magazine - BLUEMARK MAG BN-ZB - 5146192



Magazine

---

## Printer - BLUEMARK ID - 1003334

### Accessories

#### Printing system accessories

Ink cartridge - BM ID-CARTR. BK - 1044345



Replacement UV fluid, 23 ml, color: black

---

Ink cartridge - BM ID-DUMMY CARTR. BK - 1044351



Dummy cartridge for transportation, color: black

---

Original packaging - BM ID-CARDBOARD BOX - 1044361



Original packaging for transportation

---

Cleaning cartridge - BM ID-CLEANING CARTR. - 1044350

