

# Mounting material - PACT-FAST-MNT-W13-L65 - 2276625

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The transformer quick-action mechanism enables the lightning-fast mounting of PACT current transformers on the power rail. The installation can be completed easily by hand without the use of tools. Fixing pins: 65 mm, holding latches: 13 mm

RoHS

## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 658348
GTIN	4046356658348
Weight per Piece (excluding packing)	55.200 g
Custom tariff number	39269097
Country of origin	China

## Technical data

### Note

Note	The 16 mm wide converter attachment can also be used for larger current transformers if the length of the fixing pins is sufficient.
------	--

### Dimensions

Width	13 mm
Depth	65 mm

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 120 °C
---------------------------------	-------------------

### Connection data

Torque	0.4 Nm
--------	--------


### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# Mounting material - PACT-FAST-MNT-W13-L65 - 2276625

## Drawings

Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 10.0.1	27219290
eCl@ss 4.0	27210900
eCl@ss 4.1	27210900
eCl@ss 5.0	27210900
eCl@ss 5.1	27210900
eCl@ss 6.0	27149200
eCl@ss 7.0	27149223
eCl@ss 8.0	27219290
eCl@ss 9.0	27219290

### ETIM

ETIM 4.0	EC002048
ETIM 5.0	EC002498
ETIM 6.0	EC002498
ETIM 7.0	EC002498

### UNSPSC

UNSPSC 6.01	30211501
UNSPSC 7.0901	39121019

# Mounting material - PACT-FAST-MNT-W13-L65 - 2276625

## Classifications

### UNSPSC

UNSPSC 11	39121006
UNSPSC 12.01	39121006
UNSPSC 13.2	39121006

## Accessories

### Necessary add-on products

Current transformer - PACT MCR-V2- 4012- 70 - 2277284



Window-type current transformer, primary current can be selected between 75...1000 A AC; secondary current can be selected as 1 A AC or 5 A AC; accuracy class can be selected as 0.5 or 1; rated power can be selected

Current transformer - PACT MCR-V2-4012- 70- 250-5A-1 - 2277116



Window-type current transformer, 250 A AC primary current; 5 A AC secondary current; accuracy class 1; 5 VA rated power

Current transformer - PACT MCR-V2-4012- 70- 300-5A-1 - 2277679



Window-type current transformer, 300 A AC primary current; 5 A AC secondary current; accuracy class 1; 7.5 VA rated power

Current transformer - PACT MCR-V2-4012- 70- 400-5A-1 - 2277129



Window-type current transformer, 400 A AC primary current; 5 A AC secondary current; accuracy class 1; 7.5 VA rated power

## Mounting material - PACT-FAST-MNT-W13-L65 - 2276625

### Accessories

Current transformer - PACT MCR-V2-4012- 70- 500-5A-1 - 2277682



Window-type current transformer, 500 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

---

Current transformer - PACT MCR-V2-4012- 70- 600-5A-1 - 2277132



Window-type current transformer, 600 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

---

Current transformer - PACT MCR-V2-4012- 70- 750-5A-1 - 2277695



Window-type current transformer, 750 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

---

Current transformer - PACT MCR-V2-4012- 70- 800-5A-1 - 2277145



Window-type current transformer, 800 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

---

Current transformer - PACT MCR-V2-4012- 70-1000-5A-1 - 2277158



Window-type current transformer, 1000 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

---

## Mounting material - PACT-FAST-MNT-W13-L65 - 2276625

### Accessories

Current transformer - PACT MCR-V2- 5012- 85 - 2277297



Window-type current transformer, primary current can be selected between 100...1500 A AC; secondary current can be selected as 1 A AC or 5 A AC; accuracy class can be selected as 0.5 or 1; rated power can be selected

---

Current transformer - PACT MCR-V2-5012- 85- 100-5A-3 - 2276104

diameter: , length of signal cable:

---

Current transformer - PACT MCR-V2-5012- 85- 150-5A-1 - 2276117



Window-type current transformer, 150 A AC primary current; 5 A AC secondary current; accuracy class 1; 3.75 VA rated power

---

Current transformer - PACT MCR-V2-5012- 85- 200-5A-1 - 2276120



Window-type current transformer, 200 A AC primary current; 5 A AC secondary current; accuracy class 1; 5 VA rated power

---

Current transformer - PACT MCR-V2-5012- 85- 250-5A-1 - 2276133



Window-type current transformer, 250 A AC primary current; 5 A AC secondary current; accuracy class 1; 7.5 VA rated power

---

Current transformer - PACT MCR-V2-5012- 85- 300-5A-1 - 2276146



Window-type current transformer, 300 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

## Mounting material - PACT-FAST-MNT-W13-L65 - 2276625

### Accessories

Current transformer - PACT MCR-V2-5012- 85- 400-5A-1 - 2277161



Window-type current transformer, 400 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

---

Current transformer - PACT MCR-V2-5012- 85- 500-5A-1 - 2276159



Window-type current transformer, 500 A AC primary current; 5 A AC secondary current; accuracy class 1; 15 VA rated power

---

Current transformer - PACT MCR-V2-5012- 85- 600-5A-1 - 2276162



Window-type current transformer, 600 A AC primary current; 5 A AC secondary current; accuracy class 1; 15 VA rated power

---

Current transformer - PACT MCR-V2-5012- 85- 600-5A-1 - 2277174



Window-type current transformer, 600 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

---

Current transformer - PACT MCR-V2-5012- 85- 750-5A-1 - 2276175



Window-type current transformer, 750 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

---

## Mounting material - PACT-FAST-MNT-W13-L65 - 2276625

### Accessories

Current transformer - PACT MCR-V2-5012- 85- 800-5A-1 - 2277187



Window-type current transformer, 800 A AC primary current; 5 A AC secondary current; accuracy class 1; 10 VA rated power

---

Current transformer - PACT MCR-V2-5012- 85-1000-5A-1 - 2277190



Window-type current transformer, 1000 A AC primary current; 5 A AC secondary current; accuracy class 1; 15 VA rated power

---

Current transformer - PACT MCR-V2-5012- 85-1250-5A-1 - 2277200



Window-type current transformer, 1250 A AC primary current; 5 A AC secondary current; accuracy class 1; 15 VA rated power

---

Current transformer - PACT MCR-V2-5012- 85-1500-5A-1 - 2276188



Window-type current transformer, 1,500 A AC primary current; 5 A AC secondary current; accuracy class 1; 15 VA rated power

---