

Tool bag, equipped - TOOL-BAG - 1212504

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Toolbag, with laptop and document compartment, equipped with: cable cutter, diagonal cutter, stripping pliers, insulation stripper, crimp tool set, Combination, needle-nose, and water pump pliers, VDE screwdriver bladed: 0.4x2.5/0.5x3.0/1.0x4.0/1.0x5.5 crosshead: PHO/PH1/PH2 Control cabinet key, voltage tester, ferrule box Blades, tape measure, toolbag

Your advantages

- Rugged and heavy-duty tool bags
- Universal tool sets, with cutting, stripping, crimping, and testing tools from the TOOL fox tool range

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356528405
Weight per Piece (excluding packing)	7,600.000 g
Custom tariff number	82060000
Country of origin	Germany

Technical data

Dimensions

Length (b)	410 mm
Width (a)	225 mm
Depth	225 mm
Height (c)	340 mm

General

Weight	1.73 kg
--------	---------

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Tool bag, equipped - TOOL-BAG - 1212504

Articles in set

Cable-cutting tool - CUTFOX 25 VDE - 1212127



Cable cutter, precision blade with macro-notching, for copper and aluminum up to 70 mm², VDE 1000 V AC/1500 V DC tested

Diagonal cutter - CUTFOX-S VDE - 1212207



Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested

Stripping tool - WIREFOX 10 - 1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

Stripping tool - WIREFOX-D 40 - 1212161



Stripping tool, for stripping cables of 4.5 mm - 40 mm-Ø, insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

Crimping pliers set - CRIMPFOX-M SET - 1212093



Crimping pliers set, consisting of CRIMPFOX-M (pliers) and dies for insulated cable lugs 0.5 ... 2.5 mm² (1212074), non-insulated conduit lugs 0.5 ... 6 mm² (1212079) and ferrules 0.25 ... 10 mm² (1212080) and 16/25 mm² (1212081).

Tool bag, equipped - TOOL-BAG - 1212504

Articles in set

Tool - UNIFOX-C VDE - 1212202



Combination pliers, notched gripping surface, VDE 1000 V AC/1500 V DC tested, size: 180 mm

Tool - UNIFOX-P VDE - 1212204



Needle-nose pliers with blade, notched grip area, VDE 1000 V AC/1500 V DC tested

Tool - UNIFOX-WP - 1212365



Water pump pliers, with groove joint, grip areas with dual notching, acc. to VDE ISO 8976

Screwdriver - SZS 0,4X2,5 VDE - 1205037



Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip

Screwdriver - SZS 0,5X3,0 VDE - 1207404



Screwdriver, slot-headed, VDE insulated, size: 0.5 x 3.0 x 100 mm, 2-component grip, with non-slip grip

Tool bag, equipped - TOOL-BAG - 1212504

Articles in set

Screwdriver - SZS 1,0X4,0 VDE - 1205066



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip

Screwdriver - SZS 1,0X6,5 VDE - 1205079



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 6.5 x 150 mm, 2-component grip, with non-slip grip

Screwdriver - SZK PH0 VDE - 1205147



Screwdriver, PH crosshead, VDE insulated, size: PH 0 x 80 mm, 2-component grip, with non-slip grip

Screwdriver - SZK PH1 VDE - 1205150



Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip

Screwdriver - SZK PH2 VDE - 1205163



Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip

Tool bag, equipped - TOOL-BAG - 1212504

Articles in set

Voltage tester - DUSPOL EXPERT - 1209091



Voltage tester, for DC and AC voltages from 12 V to 1000 V AC/1000 V DC, IP65

Control cabinet key - USS 4 - 1203149



Control cabinet key, metal, for all common types of control cabinet

Range box - AI SORTI BOX RD - 3202960



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

Tool bag, unequipped - TOOL-BAG EMPTY - 1212500



Tool bag, with document and laptop compartments, unequipped

Measuring instrument - MEASURING TAPE 5M I/M - 1200304



Measuring tape with automatic tape feed and locking mechanism, measuring rail: imperial/metric, length: 5 m

Classifications

eCl@ss

eCl@ss 10.0.1	21045003
eCl@ss 4.0	21043000

Tool bag, equipped - TOOL-BAG - 1212504

Classifications

eCl@ss

eCl@ss 4.1	21043000
eCl@ss 5.0	21049000
eCl@ss 5.1	21049000
eCl@ss 6.0	21049000
eCl@ss 7.0	21045003
eCl@ss 8.0	21045003
eCl@ss 9.0	21045003

ETIM

ETIM 3.0	EC000149
ETIM 4.0	EC000149
ETIM 5.0	EC000149
ETIM 6.0	EC000149
ETIM 7.0	EC000149

UNSPSC

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121410
UNSPSC 13.2	27113201
UNSPSC 18.0	27113201
UNSPSC 19.0	27113201
UNSPSC 20.0	27113201
UNSPSC 21.0	27113201

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01750
-----	--	--------------------------

