

Touch panel - TP 3070W/WT - 2403465

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Rugged-Touch panel with 17.8 cm/7" TFT-display (Analog resistive (GFG)), 800 x 480 pixel(s) (WVGA), 16.7 million colors, Arm® Cortex®-A8, 1000 MHz, 2x USB host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7 and user software: Visu+. (bus system: without)


Similar figure

Your advantages

- Display can be read in sunlight
- Can be operated when wearing work gloves
- Resistant to UV and IR radiation
- Resistant to environmental influences, such as salt spray, termites, and chemicals
- Weatherproof thanks to IP67 protection



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 382302
GTIN	4055626382302
Weight per Piece (excluding packing)	1,100.000 g
Custom tariff number	84714100
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Outer dimensions: width, height, depth	234 mm x 174 mm x 5 mm (Dimensions of the front plate)
Installation dimensions: width, height, depth	200 mm x 140 mm x 48 mm (Mounting cutout, depth with bus if bus system present in the device)

Display

Touch panel - TP 3070W/WT - 2403465

Technical data

Display

Display	17.8 cm/7" TFT
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	Analog resistive (GFG)
Readability in sunlight	yes
Brightness	400 cd/m ² , typical (adjustable)
Backlighting	LED
Display backlight MTBF	50000 h
Colors	16.7 million colors
Reading angle left	70 °
Reading angle right	70 °
Reading angle top	60 °
Reading angle bottom	60 °

Computer data

Processor	Arm® Cortex®-A8, 1000 MHz
Operating system	Windows® Embedded Compact 7
User software	Visu+
RAM	512 MB LPDDR SDRAM 1 MB SRAM
Mass storage	NAND-Flash, 1 GB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x USB host 2.0
Bus system	without
Slots	1x SD
Realtime clock	Yes
Service life of battery	5 years (typical)

General

Extras	Integrated acoustic signal (buzzer)
Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated
Mounting type	Bolt fixing
Weight	1100 g

Ambient conditions

Degree of protection	IP67 (front), IP20 (back)
	NEMA 4X
Ambient temperature (operation)	-32 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Permissible humidity (operation)	5 % ... 95 % (Front)
	20 % ... 85 % (On the rear)
Vibration (operation)	1g, according to EN 60068-2-6

Touch panel - TP 3070W/WT - 2403465

Technical data

Ambient conditions

Shock	15g, according to IEC 60068-2-27
-------	----------------------------------

Device supply

Typical current consumption	0.4 A
Power supply unit	24 V DC ±20 %

Standards and Regulations

Shock	15g, according to IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 15;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27330200
eCl@ss 4.1	27330200
eCl@ss 5.0	27330200
eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242302
eCl@ss 8.0	27242302
eCl@ss 9.0	27330201

ETIM

ETIM 4.0	EC001412
ETIM 5.0	EC001412
ETIM 6.0	EC001412
ETIM 7.0	EC001412

UNSPSC

UNSPSC 13.2	43211904
UNSPSC 18.0	43211904
UNSPSC 19.0	43211904
UNSPSC 20.0	43211904
UNSPSC 21.0	43211904

Approvals

Approvals

Touch panel - TP 3070W/WT - 2403465

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 205795
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 205795
cULus Listed			

Accessories

Accessories

Battery module

Battery / accumulator - HMI BATTERY - 2701383

Lithium battery



Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for analog-resistive HMIs, silver coated. Delivery includes self-adhesive pen holder.

Touch panel - TP 3070W/WT - 2403465

Accessories

PCB plug

Printed-circuit board connector - MC 1,5/ 3-STF-3,5 BD:1-3 - 1751312



PCB connector, nominal current: 8 A, rated voltage (III/2): 160 V, Nominal cross section: 1.5 mm², number of positions: 3, pitch: 3.5 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

Storage medium

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB