



VT-7617 GU10 GARDEN LAMP,ALUMINIUM BODY -BLACK IP54

Dimensions
80x80x500mm

SKU:7567

3 YEARS
WARRANTY



Technical Information

Holder Type: **GU10**

Rated Load: **Max 35W**

Body Type: **Aluminium Body + Opal PC Diffuser**

IP Rating: **IP54**

Dimmable: **No**

Warranty (Years): **3**

Operation Temperature: **-20? to 45?**

Input Power: **AC:220-240V, 50/60Hz**

Features

- ✓ Perfect replacement for traditional wall fittings
- ✓ Designed with an Ingress protection of IP54
- ✓ Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only - Light not included)
- ✓ Easy to Install and low maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

Packaging

Unit Details

Gross Weight(GW) Kgs	1.05
Unit CBM	0.004131

Listing Details

EAN Code	3800157636407
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	4
Qty Per Pallet	200

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES