



**6W**

VT-2013 13W LED DOWNLIGHT COLORCODE:5000K DIMMABLE

Lumens <b>420</b>	Beam Angle <b>120</b>	Dimensions <b>?120x120x12mm</b>
----------------------	--------------------------	------------------------------------

Day White  
SKU:704

**5 YEARS**  
WARRANTY



## Technical Information

Output Voltage:	DC:12-24V	LED Chip Type:	SMD
Watts:	6	IP Rating:	IP20
Lumens:	420	Dimmable:	No
Shape:	Square	Warranty (Years):	5
Beam Angle:	120	PF:	>0.5
Cutting Size:	?110x110mm	CRI:	>80
Unit Color:	White	Operation Temperature:	-20°C to 45°C
Body Type:	Aluminium	Input Power:	AC:85-265V,50/60Hz
Long life:	30,000 Hours	Sensor Compatibility:	Yes

## Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs 0.2275

Unit CBM 0.000756

## Listing Details

EAN Code 3800157641609

Commodity Code 9405403990

## Master Box Packaging

Master Box Qty (Pcs Per Carton) 40

Qty Per Pallet 1600

READY STOCKS IN  
**UK & EU**



Dispatch within  
24 Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES