

40W

VT-6140 40W LED PANEL 595*595MM COLORCODE:6400K SQUARE IP65


Lumens 4400	Beam Angle 120	Dimensions 595x595x12mm
-----------------------	--------------------------	-----------------------------------

White
SKU:6330



Technical Information

Instant Start:	0-100% in 11s	LED Chip Type:	SMD
Watts:	40	IP Rating:	IP65
Lumens:	4400	Dimmable:	No
Shape:	Square	Warranty (Years):	5
On/Off Cycles:	>20000	PF:	>0.9
Beam Angle:	120	CRI:	>80
Unit Color:	White	Operation Temperature:	-25 to +50°C
Body Type:	Aluminium + PS	Input Power:	DC:25-42V
Energy Rating:	A++	Sensor Compatibility:	Yes
Long life:	30,000 Hours		



Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	3.7
Length(Box)mm	620
Width(Box)mm	40
Height(Box)mm	660
Unit CBM	0.016368

Listing Details

EAN Code	3800157620086
Commodity Code	9405403990



Master Box Packaging

Master Box Qty (Pcs Per Carton)	6
Qty Per Pallet	72

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES