


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2014441208](#)
Status: **Active**
Overview: [Nano-Fit Power Connectors](#)
Description: Nano-Fit Plug Housing, TPA Capable, 2.50mm Pitch, Dual Row, 8 Circuits, Black, Panel Mount, Glow-Wire Capable

Documents:

| | |
|---|---|
| 3D Model | Packaging Specification 2014441000-PK-000 (PDF) |
| 3D Model (PDF) | Datasheet (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification 2014471000-PS-000 (PDF) | |



General

| | |
|----------------|---|
| Product Family | Crimp Housings |
| Series | 201444 |
| Application | Power, Wire-to-Wire |
| Overview | Nano-Fit Power Connectors |
| Product Name | Nano-Fit |
| UPC | 191130026609 |

Physical

| | |
|-------------------------------|--------------------------------|
| Circuits (maximum) | 8 |
| Color - Resin | Black |
| Gender | Plug |
| Glow-Wire Capable | Yes |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 1.070/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | Yes |
| Pitch - Mating Interface | 2.50mm |
| Pitch - Termination Interface | 2.50mm |
| Polarized to Mating Part | Yes |
| Temperature Range - Operating | -40° to +105°C, -40° to +115°C |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|-------------------|
| Packaging Specification | 2014441000-PK-000 |
| Product Specification | 2014471000-PS-000 |
| Sales Drawing | 2014441000-SD-000 |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[201444 Series](#)

Mates With

Nano-Fit Receptacle Housing [1053081208](#)

Use With

Nano-Fit Crimp Terminal [201447](#)

Nano-Fit TPA Retainer [105325](#)