

Dual HDMI Monitor USB-C Docking Station with 60W Power Delivery

Product ID: DK30CHHPDUK



This USB-C docking station is ideal for use in large organizations to meet widespread office productivity requirements and compatibility with all USB-C and Thunderbolt 3 laptops. The USB-C dock features support for Dual HDMI monitors, 60W Power Delivery 3.0, fast-charge, and both USB-C and USB-A peripheral ports.

Dual Full HD 1080p HDMI Displays

The USB-C docking station adds dual HDMI monitors support to your workstation, with full high definitions resolutions of 1920x1080 or 1920x1200 at 60Hz. With more screen space, you can access multiple applications and reference material on one display while composing on the other.

Charge Devices via USB-C & USB-A

The USB-A and USB-C charge ports can charge your smartphone, tablet or other USB peripherals whether you're working or away from your desk, and even if you disconnect your laptop.

60W Power Delivery

Using a single cable, the dock powers and charges your laptop as you work with 60W PD for faster charging, using the 90W power adapter.

Convenient Setup with a Modest Desktop Footprint

With a smaller size and extended length 3.3' (1 meter) host cable, this USB-C dock fits easily into a workspace environment. Even where desk space is limited, this dock can be mounted to the wall, monitor or underneath the desk with StarTech.com mounting brackets (SSPMSUDWM & SSPMSVESA). These mounting brackets are specifically designed for our docks and hubs to give you the customized setup you need.

The Connections You Need

Connect your devices with four USB 3.1 ports: 1x USB[CC2] -C and 3x USB-A. Fast-charge your USB-C or USB-A smartphone. The dock provides a GbE port (Wake-on-LAN) and a 3.5 mm 4-position headset audio jack. It also includes a security lock slot (K-slot) to protect against theft.

The IT Pro's Choice Since 1985

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

DK30CHHPDUK is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Features

- Create a dual monitor docking station with support for dual 1080p (60Hz) HDMI monitors
- Power and charge your laptop battery while you work with up to 60W Power Delivery
- Connect more peripheral devices with 1x USB-C and 3x USB-A ports and charge mobile devices with 1x USB-C and 1x USB-A convenient front facing fast charge ports
- Compact design saves space and supports a wide variety of desktop setup configurations with an extended 1-meter USB-C host cable and mounting holes to use with optional mounting brackets
- Provide additional security using the built-in k-slot for StarTech.com cable locks

| | | |
|---------------------|-----------------------------|--|
| Hardware | Warranty | 3 Years |
| | 4K Support | No |
| | Audio | Yes |
| | Bus Type | USB 3.1 Gen 1 |
| | Chipset ID | DisplayLink DL3900 Realtek RTS5423 Realtek RTS5411E |
| | Displays Supported | 2 |
| | Interface | USB 3.1 Gen 1 |
| | K-Lock Slot | Kensington Standard Slot (K-Slot) |
| | Ports | 4 |
| | USB-C Device Port(s) | USB Power Delivery |
| | USB-C Host Connection | Yes |
| Performance | Audio Specifications | Dual-Channel 3.5mm Stereo Audio Output Single-Channel 3.5mm Microphone Input |
| | Compatible Networks | 10/100/1000 Mbps |
| | Full Duplex Support | No |
| | Maximum Data Transfer Rate | 5 Gbps (USB 3.0) 1 Gbps (Ethernet) |
| | Maximum Digital Resolutions | Dual HDMI Displays: 1080p (1920x1080, 1920x1200 @ 60Hz) |
| | Supported Charging Modes | Charging Downstream Port (CDP) |
| | Type | Copper |
| | Type and Rate | USB 3.0 - 5 Gbit/s |
| | UASP Support | Yes |
| Connector(s) | Connector Type(s) | 1 - USB Type-C (24 pin) USB 3.0 (5Gbps) Female 1 - USB 3.0 A (Fast-Charge, 9 pin) Female 2 - USB Type-A (9 pin) USB 3.0 Female 2 - HDMI 1.4 Female Output 1 - RJ-45 Female 1 - 3.5 mm Mini-Jack (4 Position) Female Female 1 - USB Type-C (Fast-Charge, 24 pin) USB 3.0 Female |

| | | |
|---------------------------------|---------------------------|--|
| Software | OS Compatibility | Windows® 7, 8, 8.1, 10 macOS 10.11, 10.12, 10.14, 10.15 Chrome OS™ v55+ |
| Power | Center Tip Polarity | Positive |
| | Input Current | 1.5A |
| | Input Voltage | 100 - 240 AC |
| | Output Current | 4.5A |
| | Output Voltage | 20V DC |
| | Plug Type | N |
| | Power Delivery | 60W |
| | Power Source | AC Adapter Included |
| Environmental | Humidity | 0% to 95% (non-condensing) at 25°C |
| | Operating Temperature | 0 to 50°C |
| | Storage Temperature | -20 to 70°C |
| Physical Characteristics | Product Height | 30.000 |
| | Product Length | 15.5 cm [6.1 in] |
| | Product Width | 80.000 |
| | Weight of Product | 310.000 |
| Packaging Information | Package Height | 85.000 |
| | Package Length | 145.000 |
| | Package Width | 231.000 |
| | Shipping (Package) Weight | 1072.000 |
| What's in the Box | Included in Package | 1 - Docking Station 1 - USB-C Host Cable (1 m) 1 - Universal Power Adapter (UK) 1 - Quick-Start Guide |

Product appearance and specifications are subject to change without notice.