



6W

VT-759 6W-WALL LAMP WITH BRIDGELUX CHIP COLORCODE:4000K
 BLACK SQUARE

Lumens 660	Beam Angle 120	Dimensions 100x100x100mm
----------------------	--------------------------	------------------------------------

Day White
 SKU:7087



Technical Information

Instant Start: 0-100% in 11s	IP Rating: IP65
Watts: 6	Dimmable: No
Lumens: 660	Warranty (Years): 2
Shape: Square	PF: >0.45
Beam Angle: 120	CRI: >80
Unit Color: Black	Operation Temperature: -25 to +50°C
Body Type: Aluminium	Input Power: AC:220-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes

Features

- ✓ High Quality Bridgelux chips for reliable operation and lifetime
- ✓ Get range of up-down beams with Adjustable beam angle to feel range of aesthetics
- ✓ Constructed to high quality aluminum for efficient heat dissipation
- ✓ Cylindrical & Cubical fixtures in 3 colors to fit into range of architectural structures
- ✓ Elegant replacement for traditional up-down lighting
- ✓ Application: Perfect for living rooms, pathways, balconies, facades etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.77
Length(Box)mm	110
Width(Box)mm	110
Height(Box)mm	110
Unit CBM	0.001331

Listing Details

EAN Code	3800157616874
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	700

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES