



VT-7622 GU10 WALL FITTING, STAINLESS STEEL BODY- 2 WAY IP44

Dimensions
93x85x163mm

SKU:7500

3 YEARS
WARRANTY



Technical Information

Holder Type: 2XGU10

Dimmable: No

Rated Load: Max 2x35W

Warranty (Years): 3

Unit Color: STAINLESS STEEL

Operation Temperature: -25 to +50°C

Body Type: Stainless Steel

Input Power: AC:220-240V,50Hz

IP Rating: IP44

Features

- ✓ Perfect replacement for traditional wall fittings
- ✓ Designed with Ingress protection of IP44
- ✓ Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only - Light not included)
- ✓ Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

Packaging

Unit Details

Gross Weight(GW) Kgs	0.69
Unit CBM	0.0017493

Listing Details

EAN Code	3800157617598
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	16
Qty Per Pallet	560

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES