



VT-7651 SLEEK GU10 WALL FITTING ROUND-BLACK 1 WAY IP44

Dimensions  
**92x68x80mm**

SKU:7508

**2 YEARS**  
WARRANTY



## Technical Information

Holder Type: **GU10**

Shape: **Round**

Rated Load: **Max 35W**

Unit Color: **Black**

Body Type: **Aluminium**

IP Rating: **IP44**

Dimmable: **No**

Warranty (Years): **2**

Operation Temperature: **-25 to +50°C**

Input Power: **AC:220-240V,50Hz**

## Features

- ✓ Perfect replacement for traditional wall fittings
- ✓ Designed with Ingress protection of IP44
- ✓ Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only - Light not included)
- ✓ Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.37
Unit CBM	0.000756

### Listing Details

EAN Code	3800157617673
Commodity Code	9405109890

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	24
Qty Per Pallet	1344

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES