



VT-7652 SLEEK GU10 WALL FITTING(ALUMINIUM) ROUND-BLACK 2 WAY IP44

Dimensions
92x68x80mm

SKU:7509

2 YEARS
WARRANTY



Technical Information

Holder Type: **GU10**

Shape: **Round**

Rated Load: **Max 2x20W**

Unit Color: **Black**

Body Type: **Aluminium**

IP Rating: **IP44**

Dimmable: **No**

Warranty (Years): **2**

Operation Temperature: **-25 to +50°C**

Input Power: **AC:220-240V,50Hz**

Features

- ✓ Perfect replacement for traditional wall fittings
- ✓ Designed with Ingress protection of IP44
- ✓ Available body type options of Aluminium and Stainless Steel
- ✓ Suitable with GU10 base lights (Fitting only - Light not included)
- ✓ Easy to Install and low Maintenance
- ✓ Application: Suitable for Pathways, Stairways, Passage, Walkways etc

Packaging

Unit Details

Gross Weight(GW) Kgs	0.575
Unit CBM	0.001344

Listing Details

EAN Code	3800157617680
Commodity Code	9405109890

Master Box Packaging

Master Box Qty (Pcs Per Carton)	16
Qty Per Pallet	672

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES