

**5W**

VT-705 5W LED WALL LIGHT COLORCODE:3000K IP20

Lumens <b>550</b>	Beam Angle <b>150</b>	Dimensions <b>175x80x96mm</b>
----------------------	--------------------------	----------------------------------

Warm White  
 SKU:8208


**2** YEARS  
 WARRANTY

**SENSOR**  
 COMPATIBLE



## Technical Information

Instant Start: 0-100% in 1/1s	Dimmable: No
Watts: 5	Warranty (Years): 2
Lumens: 550	PF: >0.5
Beam Angle: 150	CRI: >80
Unit Color: White	Operation Temperature: -20 to +45°C
Body Type: Aluminium	Input Power: AC:220-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes
IP Rating: IP20	



## Features

- ✓ Perfect choice of Interior lighting for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs	0.418
Length(Box)mm	100
Width(Box)mm	100
Height(Box)mm	180
Unit CBM	0.0018

## Listing Details

EAN Code	3800157623254
Commodity Code	9405403990



## Master Box Packaging

Inner Box Qty	20
Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	560

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES