



5W

VT-705 5W LED WALL LIGHT COLORCODE:4000K IP20

Lumens 550	Beam Angle 150	Dimensions 175 x 80 x 96mm
----------------------	--------------------------	--------------------------------------


Day White
 SKU:8232

2 YEARS
 WARRANTY



Technical Information

Watts:	5	IP Rating:	IP20
Lumens:	550	Dimmable:	No
Beam Angle:	150	Warranty (Years):	2
Unit Color:	White	PF:	>0.5
Body Type:	Aluminium	CRI:	>80
Long life:	20,000 Hours	Input Power:	AC: 220-240V,50/60Hz



Features

- ✓ Perfect choice of Interior lighting in for fabulous aesthetics and appeal
- ✓ High quality LED chips for a reliable lighting effect
- ✓ Efficient LED Driver & intruded heat sink for reliable lifespan
- ✓ Portability and ease of maintenance
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Residential, Building, Restaurants, Décor etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.505
Length(Box)mm	100
Width(Box)mm	100
Height(Box)mm	180
Unit CBM	0.0018

Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	560

Listing Details

EAN Code	3800157624756
Commodity Code	9405403990



READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES