



12W

VT-8057 12W LED UP/DOWN OUTDOOR SOFT LIGHT-LARGE
 COLORCODE:3000K GREY BODY


| | | |
|----------------------|-------------------------|-----------------------------------|
| Lumens 600 | Beam Angle 92 | Dimensions 230x100x90mm |
|----------------------|-------------------------|-----------------------------------|

Warm White
 SKU:8242



Technical Information

| | | | |
|----------------|----------------|------------------------|---------------------|
| Instant Start: | 0-100% in lt1s | IP Rating: | IP65 |
| Watts: | 12 | Dimmable: | No |
| Lumens: | 600 | Warranty (Years): | 2 |
| Beam Angle: | 92 | PF: | >0.9 |
| Unit Color: | Grey | CRI: | >80 |
| Body Type: | PC | Operation Temperature: | -20 to +45°c |
| Long life: | 30,000 Hours | Input Power: | AC:100-240V,50/60Hz |
| LED Chip Type: | SMD2835 | Sensor Compatibility: | Yes |



Features

- ✓ Perfect Soft lighting option for your Landscape, Garden & Patios
- ✓ Splendid designs made of high endurance PC material
- ✓ High quality PC material for Diffused and Controlled light output
- ✓ IP65 rated solid ingress protection
- ✓ Applications - Outdoor, Façade, Residential, Restaurants, Building and many more



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

| | |
|----------------------|---------|
| Gross Weight(GW) Kgs | 0.706 |
| Length(Box)mm | 240 |
| Width(Box)mm | 110 |
| Height(Box)mm | 100 |
| Unit CBM | 0.00264 |

Listing Details

| | |
|----------------|---------------|
| EAN Code | 3800157625821 |
| Commodity Code | 9405403990 |



Master Box Packaging

| | |
|---------------------------------|-----|
| Master Box Qty (Pcs Per Carton) | 20 |
| Qty Per Pallet | 420 |

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES