



12W

VT-8057 12W LED UP/DOWN OUTDOOR SOFT LIGHT-LARGE
 COLORCODE:4000K GREY BODY

Lumens 600	Beam Angle 92	Dimensions 230x100x90mm
----------------------	-------------------------	-----------------------------------

Day White
 SKU:8243


2 YEARS
 WARRANTY

SENSOR
 COMPATIBLE



Technical Information

Instant Start:	0-100% in lt1s	IP Rating:	IP65
Watts:	12	Dimmable:	No
Lumens:	600	Warranty (Years):	2
Beam Angle:	92	PF:	>0.9
Unit Color:	Grey	CRI:	>80
Body Type:	PC	Operation Temperature:	-20 to +45°c
Long life:	30,000 Hours	Input Power:	AC:100-240V,50/60Hz
LED Chip Type:	SMD2835	Sensor Compatibility:	Yes



Features

- ✓ Perfect Soft lighting option for your Landscape,Garden & Patios
- ✓ Splendid designs made of high endurance PC material
- ✓ High quality PC material for Diffused and Controlled light output
- ✓ IP65 rated solid ingress protection
- ✓ Applications - Outdoor, Façade, Residential, Restaurants, Building and many more

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.706
Length(Box)mm	240
Width(Box)mm	110
Height(Box)mm	100
Unit CBM	0.00264

Listing Details

EAN Code	3800157625838
Commodity Code	9405403990



Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	420

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES