



20W

VT-821 20W LED WALL LAMP COLOURCODE:3000K WHITE BODY,IP44

Lumens <b>2000</b>	Beam Angle <b>150</b>	Dimensions <b>610x90x35mm</b>
-----------------------	--------------------------	----------------------------------

Warm White  
SKU:8535

**2 YEARS**  
WARRANTY

**SENSOR**  
COMPATIBLE



## Technical Information

Watts:	20	LED Chip Type:	SMD
Lumens:	2000	IP Rating:	IP44
On/Off Cycles:	>15000	Dimmable:	No
Beam Angle:	150	Warranty (Years):	2
Unit Color:	White	CRI:	>80
Body Type:	Aluminium	Input Power:	AC:220-240V,50/60Hz
Long life:	20,000 Hours	Sensor Compatibility:	Yes

## Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs	1.024
Unit CBM	0.00248

## Listing Details

EAN Code	3800157638692
Commodity Code	9405403990

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	500

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES