

PULSE



LOGO30 including GOBO PACK

Model: LOGO30

Please read these instructions carefully before use and retain for future reference.

IMPORTANT SAFETY INFORMATION

- When using electrical appliances basic safety precautions should always be followed.
- Check the product before use for any damage. Should you notice any damage on the cable or casing, do not use.
- Check that the voltage indicated on the rating plate corresponds with that of the local network before connecting the product to the mains power supply.
- Keep this product away from rain and moisture.
- For indoor use only.

Caution: Never look directly into the light source.

- Always disconnect from the mains when the product is not in use or before cleaning.
- Do not operate or store in an environment of high humidity or where moisture may enter the product as this can reduce insulation and lead to electric shock.


Safety Information for Installation and Operation

- When installing, make sure that the product is not exposed to extreme heat, moisture or dust.
- If you're using a smoke machine, make sure that the product is never exposed to the direct smoke jet and is installed at least 0.5m away.
- The ambient temperature must always be between -20°C and 40°C. Keep away from air-conditioning units and heaters.
- The relative humidity must not exceed 50% with an ambient temperature of 40°C.
- This product must only be operated in an altitude between -20 and 2000m above sea level.
- The minimum distance between the light-output and the illuminated surface must be more than 0.5m.
- This device is allowed to be installed via a mounting bracket. In order to have sufficient ventilation, leave 50cm of free space around the device.
- The housing must not touch any surrounding surfaces or objects.
- Operate the product only after having familiarised yourself with its functions. Do not allow operation by persons unqualified.
- A secondary means of suspension must be provided, such that in the event of a failure of the primary suspension, no part of the luminaire can fall.
- The operator must make sure that safety related matters are observed and that the installation is approved by a qualified installer before taking into operation for the first time.

WHATS IN THE BOX

- Light unit and mounting bracket.
- Mains lead.
- Additional mounting accessories.
- Pack of GOBO (GO Before Optics) discs.
- Instruction manual.

INSTALLATION



1	Safety suspension attachment
2	Mounting
3	Mains input connection
4	Rotation ON/OFF switch
5	Cooling fan

- Secure the luminaire using the attached mounting bracket and adjust the projection angle by loosening the thumb wheels and rotating the lamp assembly then re-tighten the thumb wheels.

OPERATION

- Connect the mains lead and turn on the power and the LED will illuminate.
- To start the rotation of the projected image press the red switch to the ON position.
- To change the GOBO filter disc unscrew the two thumb screws on the bottom of the lamp assembly and extract the holder.
- Extract the wire circlip from the front recess and press out the filter disc.
- Replace the filter disc and circlip then refit the holder and tighten the thumb screws.
- To focus the projection turn the outer knurled wheel around the lens until the projected image is in focus.

CLEANING & MAINTENANCE

- Disconnect from the mains before starting the maintenance operation.
- Frequent cleaning is recommended. Use a soft lint-free moistened cloth.
- Do not use any chemicals, abrasives or solvents that could damage the device.
- There are no user-serviceable parts in this product. Refer all servicing to qualified personnel.

SPECIFICATIONS

Voltage	AC 220-240V 50Hz
Power	30W
LED source	1pcs 30W LED
Fuse	F3AL250V
GOBO dimension	28.6mm OD - 26mm image (1mm max thickness)
Working environment	-20°C ~ 40°C
Dimensions W x H x D	180 x 192 x 220mm
Weight	1.76kg



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.



Made in China. PR2 9PP
Man Rev 1.1