

acer

Acer recommends Windows 10 Pro.



TravelMate P2

 Windows 10



Faster memory speed



Up to 4X faster storage performance




MIL-STD 810G Compliant



Up to 14-Hours Battery Life



180-Degree lay flat




Narrow Bezel



TPM



Cortana with voice



Product views	1. Webcam 2. 15.6" display 3. DC-in jack 4. NO Optical drive	5. USB ports 6. SD card reader 7. Keyboard 8. Touchpad	9. Power key 10. Headset/speaker jack 11. USB 3.1 Gen 1 port with power-off charging 12. HDMI® port	13. VGA port 14. USB Type-C port with DC-in 15. RJ-45 port 16. Kensington lock slot
Operating system^{1,2}	Windows 10 Pro 64-bit			
CPU and chipset¹	Intel® Core™ i5-8250U Processor 6M Cache, up to 3.40 GHz			
Memory^{1,3,4,5}	Dual-channel DDR4 SDRAM support • 8 GB of onboard DDR4 system memory Up to 24 GB of DDR4 system memory			
Display⁶	15.6" display with IPS (In-Plane Switching) technology, Full HD 1920 x 1080, Acer ComfyView™ LED-backlit TFT LCD • 16:9 aspect ratio • Wide viewing angle up to 170 degrees • Ultra-slim design Mercury free, environment friendly			
Graphics	Intel® UHD Graphics 620			
Audio⁶	• Built-in digital microphone • Two built-in stereo speakers			
Storage^{1,7,8}	Solid state drive • 256 GB, PCIe Gen3 8 Gb/s			
Webcam¹	HD camera with 1280 x 720 resolution and 720p HD audio/video recording			
Wireless and networking¹	WLAN <ul style="list-style-type: none"> Intel® Dual Band Wireless-AC 8265, 802.11ac/a/b/g/n wireless LAN with Acer Nplify™ Operates at 2.4 GHz and 5 GHz 2x2 MIMO technology Supports MU-MIMO Intel® vPro™ technology WLAN <ul style="list-style-type: none"> Intel® Dual Band Wireless-AC, 802.11ac/a/b/g/n wireless LAN with Acer Nplify™, featuring 2x2 MIMO technology WPAN <ul style="list-style-type: none"> Bluetooth® 4.2 LAN <ul style="list-style-type: none"> Gigabit Ethernet, Wake-on-LAN ready 			
Security	Discrete Trusted Platform Module (TPM) solution Acer ProShield Security Manager including: Facial Recognition Login Data Protection: File Encryption & Decryption, Personal Secure Drive Data Removal: File Shredder Acer Bio-Protection fingerprint solution, featuring computer protection and Windows Hello Certification BIOS user, supervisor, HDD passwords Kensington lock slot			
Dimensions and weight^{1,8,9}	Dimensions: 365 (W) x 256 (D) x 19.99 (H) mm (14.37 x 10.08 x 0.79 inches) Weight: 1.83 kg (4.03 lbs.) with 3-cell battery pack, one SSD			
Power adapter and battery^{1,10}	Power adapter • 3-pin 45 W AC adapter (P215-51 only) Battery • 51.5 Wh 4515 mAh 11.4 V 3-cell Li-ion battery pack			
Input and control	Keyboard 103-/104-/107-key FineTip keyboard with independent standard numeric keypad, international language support, power button Touchpad Multi-gesture touchpad, supporting two-finger scroll; pinch; gestures to open Cortana, Action Center, multitasking; application commands • Microsoft Precision Touchpad certification • Moisture resistant Multi-gesture secure touchpad, supporting two-finger scroll; pinch; gestures to open Cortana, Action Center, multitasking; Fingerprint application commands • Microsoft Precision Touchpad certification • Windows Hello Certification			
Windows Store 13 Apps	In-House <ul style="list-style-type: none"> Apps • Acer Collection Quick Access Tools <ul style="list-style-type: none"> MS Remote Desktop 			
System compliance¹²	• ENERGY STAR® • Wi-Fi® • EPEAT® registered			
Warranty	2 years warranty, One-year International Travelers Warranty (ITW)		Optional Acer Care Plus 3 Jahre Vor-Ort-Service (nbd) (SV.WNBAP.A12)	
Acer recommends Windows 10 Pro. 1. Specifications vary depending on model. 2. 64-bit software is required to enjoy the advantages of 64-bit processing. 3. Shared system memory may be allocated to support graphics, depending on system memory size and other factors. Actual system memory available to the operating system will be reduced by any memory used by the graphics solution and resources required by the operating environment. 4. Memory speed may vary, depending on the CPU, chipset or memory fitted. 5. A 64-bit operating system is required to enjoy the ultimate performance of 4 GB or higher memory. 6. All brands and product names mentioned herein include trademarks of their respective companies and are used solely to describe or identify the products. 7. 1 GB is 1 billion bytes, 1 TB is 1000 GB. Actual formatted capacity is less and may vary depending on preloaded materials and operating environment. Acer Recovery Management uses a portion of the stated hard disk capacity as dedicated backup space. 8. Minor variations in system dimensions are possible due to the manufacturing process. 9. Weight may vary depending on product configuration, vendor components, manufacturing variability, and selected options. 10. Listed battery life is based on MobileMark 2014® productivity mode testing with wireless on. Details of MobileMark 2014® testing are available at www.bapco.com. Battery life rating is for comparison purposes only. Actual battery life varies by model, configuration, application, power management settings, operating conditions, and features used. A battery's maximum capacity decreases with time and use. 11. Bundled software may vary depending on hardware configuration, OS and regional availability. 12. EPEAT® registration varies by country. See http://www.epeat.net/ for registration status for each country.				

In a continuing effort to improve the quality of our products, information in this document is subject to change without notice. Images shown are only representations of some of the configurations available for this model. Availability may vary depending on region.
 As a phenomenon known to thin-film transistors (TFTs), liquid crystal displays (LCDs) commonly exhibit a small number of discoloration dots, as so-called "non-conforming pixels." This phenomenon is a limitation of TFT LCD technology, not a product defect, and as such is not covered by Acer's warranty.
 © 2019. All rights reserved.
 Microsoft and Windows are registered trademarks of Microsoft Corporation.
 Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Core Inside, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi, Xeon Inside, and Intel Optane are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries.

About Acer

Founded in 1976, Acer is now one of the world's top ICT companies and has a presence in over 160 countries. As Acer looks into the future, it is focused on enabling a world where hardware, software and services will fuse with one another to open up new possibilities for consumers and businesses alike. From service-oriented technologies to the Internet of Things to gaming and virtual reality, Acer's 7,000+ employees are dedicated to the research, design, marketing, sale, and support of products and solutions that break barriers between people and technology. Please visit www.acer.com for more information.