

# PDU-10WS-V

10-Way Vertical  
Non-Surged Protected  
PDU



Telecom &  
Networking



Data centres &  
Server farms



Broadcast &  
A/V



HVAC &  
Industrial

## Cost-Effective Power Distribution For Your Applications

### Need a competitively priced but quality Power Distribution Unit (PDU) for your applications or installation?

The new **PDU-10WS-V** is a robust, non-surged protected PDU which features effective electrical distribution to its integral, 10-way, UK-socketed 3-pin sockets.

Combining a fully certified UK plug input combined with a compatible heavy load power flex means you can be assured this LMS Data PDU can work without problems, 24/7.

Ideal for data, telco and broadcast applications, with the added benefit of a low-profile, 1U high and the ability to be mounted vertically in almost all floor, telco and server enclosures via the standard mount slots.

Robust in design, with an integral neon illuminated rocker switch for assured functionality, the LMS Data PDU is designed to deliver maximum electrical power - today and tomorrow.

## specifications:

Vertical, high-density Power Distribution Unit (PDU)

**UK-plug style plug power input**

10-Way UK, 3-Pin Power Outlets

**Robust, black aluminium design for industrial use**

Neon on/off power switch for assured control

**Maximum power rating - 4000W (approx.)**

1.8 metre (approx.) power cordage

**Ideal for data, telecom, broadcast and HVAC applications**



\* Image for representation only  
Subject to change



Copyright 2017 LMS Data  
All trademarks acknowledged E&OE.  
Details subject to change